



Predator™ Fan Coil Unit Controller



Description

The LONMARK® certified Predator™ Fan Coil Unit (FCU) Controllers provide direct digital control of fan coil units. The Predator is designed to reside on a LONWORKS® network, providing seamless interaction with all LONMARK products. The Predator FCU Controller offers cost-effective flexibility by providing various input/output configurations; each designed to meet individual fan coil unit application requirements.

Features

- Conforms and is certified to the LONMARK inter-operability guidelines, enabling information sharing with other LONMARK products.
- LONMARK-compliant with space-comfort controller functional profile number 8501.
- Downloadable applications for flexibility to meet ever-changing needs.
- Field-selectable parameters allow entry and updating of setpoint and control parameters via the TALON™ Interface.
- Unique two-piece design, consisting of an Enclosure Cover with Embedded Controller Board and a separate Wiring Base, to protect electronic parts from potential damage during installation.
- Network-wide monitoring and commanding from the Room Sensor and/or Predator Controller.
- Two I/O platform configurations for application flexibility.
- Advanced PID control minimizes offset and maintains tighter setpoint control.
- Return to service from power failure without operator intervention.

Applications

The Predator FCU Controller can be configured to control a variety of fan-coil unit applications, including:

- Fan coil cooling only
- Fan coil heating only
- Two-pipe fan coil unit shared cooling and heating
- Four-pipe fan coil unit cooling and heating
- Fan coil unit with 1 to 2 stages of DX cooling and electric heat
- Fan coil unit with 1 to 2 stages of DX cooling and hot water coil

The Predator FCU Controller can also control perimeter heat, in addition to the above configurations.

Additionally, based upon availability of input and output capacity, occupancy and outdoor air temperature sensors and lighting can be controlled via these applications.

Hardware

The unique design of the Predator FCU Controllers consists of two components:

- Enclosure with Embedded Controller Board
- Wiring Base

This design reduces threat of damage to the controller board during installation and reduces service time. The wiring connections are made to the wiring base, allowing this component to be installed early in the project cycle. Additionally, if the board needs repair, the controller board can be removed easily, without disrupting the wiring connections.

Enclosure Cover with Embedded Controller Board

To further enhance the protection of the controller board, it is embedded into the enclosure cover. Installation consists of snapping the enclosure cover onto the wiring base.

The Enclosure Cover with Embedded Controller Board is available in the following configurations:

- 4 Inputs, 6 Digital Outputs, 1 Room Sensor port
- 5 Inputs, 8 Digital Outputs, 2 Analog Outputs, 1 Room Sensor port

The Controller Board communicates to all LONMARK devices via a Neuron[®]- chip. The controllers are shipped with pre-loaded applications, reducing engineering start-up time. Additionally, if facility requirements change, a new application can be quickly downloaded by a Staefa dealer.

The control application is stored in Flash memory. Flash memory allows an application to be changed without removing the existing controller or memory chip.

A quick-connect LONWORKS network port is built into each Controller Board, for initial controller setup and network-wide access.

Room Sensor

The room sensor connects to the network with a quick-connect RJ-11 jack. This streamlines installation and reduces Predator start-up time.

Spare Input/Output Points

The Predator Controller, depending upon the application, may have up to 3 input and 2 output spare points available. These points can be used for control of devices located in close proximity to the Predator Controller, reducing installations costs.

Wiring Base

The Predator Wiring Base is available in two configurations:

- Full Point
- Reduced Point


The Full Point base is designed to handle either the Full Point 5IN/8DO/2AO controller or Reduced Point 4IN / 6 DO controller . This base provides the flexibility of replacing a Reduced Point I/O-style controller with a Full Point I/O style-controller if needs change.

The Reduced Point base matches the Reduced Point 4IN/6 DO controller board style providing a cost effective solution for lower point count applications.

Specifications

Specification	
Processor Type	Neuron 3150
Processor Clock Speed	10 MHz - Neuron
Network Communication	TP/XF-10 (78.8K bps)
Memory Size	49 K Flash Memory 10 K SRAM
Local Network Communication Interface	LON port
Voltage Requirements	24 Vac @ 50/60 Hz
Power Consumption	5 VA plus loads
Ambient Operating Environment	+32°F to +122°F (0°C to +50°C) 5 to 95% RH (Non-condensing)
Agency Listings	UL/CUL 916 PAZX/PAZX7 (Enclosed Energy Management) LONMARK 3.2
Regulatory Compliance	FCC Part 15, Class B CISPR 22 Class B CE Mark Australian EMC Framework
Predator Dimensions:	6.75" H × 7" W × 2.45" D (171 mm × 178 mm × 62 mm)
Weight	2 lbs (.9 kg)

Wiring



NOTE: Input 6 (described as "internal" in diagram) is only used on the VAV version of the Predator for the Differential Pressure Sensor. It is not available on the UV, HP or FCU styles

Wiring Recommendations:

Input/AO	20 to 22 AWG
DO	18 to 22 AWG
Power	16 to 18 AWG
LONWORKS Network	22 AWG Level 4

Transformer Requirements and Recommended Voltages

Type	Class 2 , 24 Vac, 50/60 Hz
------	----------------------------

Optional Accessories

Predator Room Temperature Sensors

The Predator Room Temperature Sensors offer a wide range of features and functions. These sensors work with the Staefa TALON building automation system to deliver exceptional occupant comfort in even the most demanding application environments. The product family ranges from temperature-sensing-only variants to types that include LCD display, setpoint, and override. The sensors incorporate precision temperature sensing elements to accurately and reliably measure room temperature. The compact design results in an attractive, inconspicuous installation. A styled ventilation ring optimizes airflow through the cover for fast measurement response.

Predator Room Sensor Specifications

Dimensions	3-11/32" H × 2-1/2" W × 1-1/2" D (85 mm × 63 mm × 38 mm)
Temperature Monitoring Range	55° to 95°F (13° to 35°C)
Thermistor Resistance Value	10,000 Ohms @ 77°F (25°C)
Setpoint Range	55-95°F
Calibration Adjustments	None Required
Standard Color	White

Ordering Information

Controllers

Description	Product Number
Predator DX FCU Full Point Controller 5IN 8DO 2AO	587-221
5 IN (2) 100K Ω Thermistor / (3) 0-10 Vdc or Dry Contact	
8 DO 24 Vac, 12VA, Triac	
2 AO 0-10 Vdc	
1 RS 10K Ω Thermistor Room Sensor	
Predator CH/HW FCU Full Point Controller 5IN 8DO 2AO	587-220
5 IN (2) 100 K Ω Thermistor / (3) 0-10 Vdc or Dry Contact	
8 DO 24 Vac, 12VA, Triac	
2 AO 0-10 Vdc	
1 RS 10K Ω Thermistor Room Sensor	
Predator DX FCU Reduced Point Controller 4IN 6DO	587-211
4 IN (2) 100 K Ω Thermistor / (2) 0-10 Vdc or Dry Contact	
6 DO 24 Vac, 12VA, Triac	
1 RS 10K Ω Thermistor Room Sensor	
Predator CH/HW FCU Reduced Point Controller 4IN 6DO	587-210
4 IN (2) 100 K Ω Thermistor / (2) 0-10 Vdc or Dry Contact	
6 DO 24 Vac, 12VA, Triac	
1 RS 10K Ω Thermistor Room Sensor	

Predator Full Point Wiring Base	587-175
Termination support up to 5IN, 8DO and 2AO	
Predator Reduced Point Wiring Base	587-170
Termination support for the 4IN and 6DO	

Accessories


Description	Product Number
Predator Room Sensors	
Sensing Only	587-180
Override	587-181
Setpoint	587-182
Temperature Display	587-183 ¹
Setpoint and Override	587-184
Override and Temperature Display	587-185 ¹
Setpoint and Temperature Display	587-186 ¹
Setpoint, Override and Temperature Display	587-187 ¹
Predator Termination Connector Kit	587-171

Documentation

Description	Product Number
TALON Information Library CD	587-980

Note: 1. Sensor will display Fahrenheit or Celsius temperature.

TALON Architecture



Notice: Information in this document is based on specifications believed correct at the time of publication. The right is reserved to make changes as design improvements are introduced.
Credits: *Staeefa Control System, Raptor, Predator, and TALON* are trademarks of Siemens Building Technologies, Inc. Other products and company names herein may be the trademarks of their respective owners.



Siemens Building Technologies, Inc.
 HVAC Products
 1000 Deerfield Parkway
 Buffalo Grove, Illinois 60089
 Phone 847-215-1000
www.staeefa.com

Copyright 2001 by Siemens Building Technologies, Inc.

